



JPE6000M20DW1

DB, elite, 60Pole, 200A MCCB Twin,8 Mod+26 Mod, grey,1400x600x250mm

Technical Features

Connection

Number of accessible phases	60
-----------------------------	----

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Electric current

Rated current	200 A
---------------	-------

Breaking and opening capacity ldm	0 kA
-----------------------------------	------

Equipment

With lock	Yes
-----------	-----

Has mounting plate	No
--------------------	----

Equipped with switch	No switch
----------------------	-----------

Number of switches	0
--------------------	---

Type of busbar chassis	Fixed load chassis
------------------------	--------------------

Capacity

Number of modules	42
-------------------	----

Dimensions

Height	1400 mm
--------	---------

Width	600 mm
-------	--------

Depth	250 mm
-------	--------

Cover, door

Door/cover is transparent	No
---------------------------	----

Materials

Material	Steel
----------	-------

RAL code	7035
----------	------

Colour	Light grey
--------	------------

Safety

Protection class	Isolation class I
------------------	-------------------

Impact resistance IK	IK05
----------------------	------

Ingress Protection (IP) class	IP66
-------------------------------	------

Locking type	3-point lever Key lock
--------------	---------------------------

Architecture

Number of poles	60
-----------------	----