Product Datasheet
JPE3600NSSDS



JPE3600NSSDS1

DB, elite, 36Pole, No Incomer-DIN-SS,1200x600x250mm

Technical Features

Connection

Number of accessible phases	36

Installation, mounting

Mounting on	Surface mounting

Electric current

Rated current	250 A
Breaking and opening capacity Idm	0 kA

Equipment

With lock	Yes
Has mounting plate	No
Equipped with switch	No switch
Number of switches	0
Type of busbar chassis	Split chassis

Capacity

Number of modules	42

Weight

Weight	45 kg

Dimensions

Height	1200 mm
Width	600 mm
Depth	250 mm

Cover, door

Door/cover is transparent	No

Materials

Material	Stainless steel
Colour	Stainless steel

Safety

Protection class	Isolation class I
Impact resistance IK	IK05
Ingress Protection (IP) class	IP66
Locking type	3-point lever Key lock

Architecture

Number of poles	36

Sustainability

RoHS conform	Yes