



JPE6000S25DW1

**DB, elite, 60Pole, 250A Isolator 2x8Mod+26 Mod, grey,1400x600x250mm**

**Technical Features**

**Connection**

Number of accessible phases	60
-----------------------------	----

**Installation, mounting**

Mounting on	Surface mounting
-------------	------------------

**Electric current**

Rated current	250 A
---------------	-------

Breaking and opening capacity ldm	0 kA
-----------------------------------	------

**Equipment**

With lock	Yes
-----------	-----

Has mounting plate	No
--------------------	----

Equipped with switch	No switch
----------------------	-----------

Number of switches	0
--------------------	---

Type of busbar chassis	Fixed load chassis
------------------------	--------------------

**Capacity**

Number of modules	42
-------------------	----

**Dimensions**

Height	1400 mm
--------	---------

Width	600 mm
-------	--------

Depth	250 mm
-------	--------

**Cover, door**

Door/cover is transparent	No
---------------------------	----

**Materials**

Material	Steel
----------	-------

RAL code	7035
----------	------

Colour	Light grey
--------	------------

**Safety**

Protection class	Isolation class I
------------------	-------------------

Impact resistance IK	IK05
----------------------	------

Ingress Protection (IP) class	IP66
-------------------------------	------

Locking type	3-point lever Key lock
--------------	---------------------------

**Architecture**

Number of poles	60
-----------------	----

**Sustainability**

RoHS conform	Yes
--------------	-----