



JPD6030M20DX1

DB, apex+, 60/30Pole,200A MCCB Twin, 8 Modules, orange, 1600x600x200mm

Technical Features

Connection

Number of accessible phases 90

Installation, mounting

Mounting on Surface mounting

Electric current

Rated current 200 A

Equipment

With lock Yes

Has mounting plate No

Equipped with switch MCCB

Number of switches 1

Type of busbar chassis Split chassis

Capacity

Number of modules 42

Weight

Weight 70 kg

Dimensions

Height 1600 mm

Width 600 mm

Depth 200 mm

Cover, door

Door/cover is transparent No

Materials

Material Steel

Colour Orange

Safety

Protection class Isolation class I

Impact resistance IK IK05

Ingress Protection (IP) class IP43

Locking type 3-point lever
Key lock

Architecture

Number of poles 96

Sustainability

RoHS conform Yes