
Product Datasheet
JPE4800M20DS



JPE4800M20DS1

DB, elite, 48Pole, 200A MCCB-DIN-SS,1400x600x250mm

Technical Features

Connection

Number of accessible phases	48

Installation, mounting

Mounting on	Surface mounting

Electric current

Rated current	200 A

Equipment

With lock	Yes
Has mounting plate	No
Equipped with switch	MCCB
Number of switches	1
Type of busbar chassis	Fixed load chassis

Capacity

Number of modules	42

Weight

Weight	59 kg

Dimensions

Height	1200 mm
Width	600 mm
Depth	250 mm

Cover, door

Door/cover is transparent	No

Materials

Material	Stainless steel
Colour	Stainless steel

Safety

Protection class	Isolation class I
Impact resistance IK	IK05
Ingress Protection (IP) class	IP66
Locking type	3-point lever Key lock

Architecture

Number of poles	48

Sustainability

RoHS conform	Yes