



JPE1812S25DX1

DB, elite, 18/12Pole, 250A Isolator Twin,8 Module,orange,1200x600x250mm

### Technical Features

#### Connection

Number of accessible phases	30
-----------------------------	----

#### Installation, mounting

Mounting on	Surface mounting
-------------	------------------

#### Electric current

Rated current	250 A
Breaking and opening capacity Idm	0 kA

#### Equipment

With lock	Yes
Has mounting plate	No
Equipped with switch	No switch
Number of switches	0
Type of busbar chassis	Split chassis

#### Capacity

Number of modules	42
-------------------	----

#### Dimensions

Height	1200 mm
Width	600 mm
Depth	250 mm

#### Cover, door

Door/cover is transparent	No
---------------------------	----

#### Materials

Material	Steel
Colour	Orange

#### Safety

Protection class	Isolation class I
Impact resistance IK	IK05
Ingress Protection (IP) class	IP66
Locking type	3-point lever Key lock

#### Architecture

Number of poles	30
-----------------	----