



JPE2400S16DX1

DB, elite, 24Pole,160A Isolator 2x8 Mod+26 Mod,orange,1000x600x250mm

Technical Features

Connection

Number of accessible phases 24

Installation, mounting

Mounting on Surface mounting

Electric current

Rated current 160 A

Breaking and opening capacity I_{dm} 0 kA

Equipment

With lock Yes

Has mounting plate No

Equipped with switch No switch

Number of switches 0

Type of busbar chassis Fixed load chassis

Capacity

Number of modules 42

Weight

Weight 43 kg

Dimensions

Height 1000 mm

Width 600 mm

Depth 250 mm

Cover, door

Door/cover is transparent No

Materials

Material Steel

Colour Orange

Safety

Protection class Isolation class I

Impact resistance IK IK05

Ingress Protection (IP) class IP66

Locking type 3-point lever
Key lock

Architecture

Number of poles 24

Sustainability

RoHS conform Yes