



JPD6030M20DW1

**DB, apex+, 60/30Pole,200A MCCB Twin, 8 Modules, grey, 1600x600x200mm**

**Technical Features**

**Connection**

Number of accessible phases 90

**Installation, mounting**

Mounting on Surface mounting

**Electric current**

Rated current 200 A

**Equipment**

With lock Yes

Has mounting plate No

Equipped with switch MCCB

Number of switches 1

Type of busbar chassis Split chassis

**Capacity**

Number of modules 42

**Weight**

Weight 70 kg

**Dimensions**

Height 1600 mm

Width 600 mm

Depth 200 mm

**Cover, door**

Door/cover is transparent No

**Materials**

Material Steel

RAL code 7035

Colour Light grey

**Safety**

Protection class Isolation class I

Impact resistance IK IK05

Ingress Protection (IP) class IP43

Locking type 3-point lever  
Key lock

**Architecture**

Number of poles 96

**Sustainability**

RoHS conform Yes