




JPE0624S40TX1

DB, elite, 400A, 6+24Pole, 400A ISO-X15.1200x600x250mm

Technical Features

Connection

Number of accessible phases	30
-----------------------------	----

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Electric current

Rated current	375 A
Breaking and opening capacity Idm	0 kA

Equipment

With lock	Yes
Has mounting plate	No
Equipped with switch	No switch
Number of switches	0
Type of busbar chassis	Hybrid chassis

Capacity

Number of modules	42
-------------------	----

Dimensions

Height	1200 mm
Width	600 mm
Depth	250 mm

Cover, door

Door/cover is transparent	No
---------------------------	----

Materials

Material	Steel
Colour	Orange

Safety

Protection class	Isolation class I
Impact resistance IK	IK05
Ingress Protection (IP) class	IP66
Locking type	3-point lever Key lock

Architecture

Number of poles	30
-----------------	----