Product Datasheet
JPE4212M16DX



JPE4212M16DX1

DB, elite, 42/12Pole, 160A MCCB Twin, 8 Modules, orange, 1400x600x250mm

Technical Features

Connection	
Number of accessible phases	54
Installation, mounting	
Mounting on	Surface mounting
Electric current	
Rated current	160 A
Equipment	
With lock	Yes
Has mounting plate	No
Equipped with switch	MCCB
Number of switches	1
Type of busbar chassis	Split chassis
Capacity	
Number of modules	42
Weight	
Weight	62 kg
Dimensions	
Height	1400 mm
Width	600 mm
Depth	250 mm
Cover, door	
Door/cover is transparent	No
Materials	
Material	Steel
Colour	Orange
Safety	
Protection class	Isolation class I
Impact resistance IK	IK05
Ingress Protection (IP) class	IP66
Locking type	3-point lever Key lock
Architecture	
Number of poles	54
Sustainability	
RoHS conform	Yes