



JPE0612S40TS1

DB, elite, 320A, 6+12Pole, 400A ISO-S.1000x600x250mm

Technical Features

Connection

Number of accessible phases	18
-----------------------------	----

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Electric current

Rated current	276 A
Breaking and opening capacity I _{dm}	0 kA

Equipment

With lock	Yes
Has mounting plate	No
Equipped with switch	No switch
Number of switches	0
Type of busbar chassis	Hybrid chassis

Capacity

Number of modules	42
-------------------	----

Weight

Weight	44 kg
--------	-------

Dimensions

Height	1000 mm
Width	600 mm
Depth	250 mm

Cover, door

Door/cover is transparent	No
---------------------------	----

Materials

Material	Stainless steel
Colour	Stainless steel

Safety

Protection class	Isolation class I
Impact resistance IK	IK05
Ingress Protection (IP) class	IP66
Locking type	3-point lever Key lock

Architecture

Number of poles	18
-----------------	----