



JPE0636S40TS1

**DB, elite, 400A, 6+36Pole, 400A ISO-S.1200x600x250mm**

**Technical Features**

**Connection**

Number of accessible phases	42
-----------------------------	----

**Installation, mounting**

Mounting on	Surface mounting
-------------	------------------

**Electric current**

Rated current	375 A
Breaking and opening capacity I <sub>dm</sub>	0 kA

**Equipment**

With lock	Yes
Has mounting plate	No
Equipped with switch	No switch
Number of switches	0
Type of busbar chassis	Split chassis

**Capacity**

Number of modules	42
-------------------	----

**Weight**

Weight	59 kg
--------	-------

**Dimensions**

Height	1200 mm
Width	600 mm
Depth	250 mm

**Cover, door**

Door/cover is transparent	No
---------------------------	----

**Materials**

Material	Stainless steel
Colour	Stainless steel

**Safety**

Protection class	Isolation class I
Impact resistance IK	IK05
Ingress Protection (IP) class	IP66
Locking type	3-point lever Key lock

**Architecture**

Number of poles	42
-----------------	----