Product Datasheet
JPE4842M20DW



JPE4842M20DW1

DB, elite, 48/42Pole, 200A MCCB Twin, 8 Modules, grey, 1600x600x250mm

Technical Features

Connection

Number of accessible phases	90

Installation, mounting

Mounting on	Surface mounting

Electric current

Rated current	200 A

Equipment

With lock	Yes
Has mounting plate	No
Equipped with switch	MCCB
Number of switches	1
Type of busbar chassis	Split chassis

Capacity

Number of modules	42

Weight

Weight	73 kg

Dimensions

Height	1600 mm
Width	600 mm
Depth	250 mm

Cover, door

Door/cover is transparent	No

Materials

Material	Steel
RAL code	7035
Colour	Light grey

Safety

Protection class	Isolation class I
Impact resistance IK	IK05
Ingress Protection (IP) class	IP66
Locking type	3-point lever Key lock

Architecture

Number of poles	90

Sustainability

RoHS conform	Yes