



JPE6030S16DS1

DB, elite, 60/30Pole, 160A ISO-DIN-SS, 1600x600x250mm

### Technical Features

#### Connection

Number of accessible phases	90
-----------------------------	----

#### Installation, mounting

Mounting on	Surface mounting
-------------	------------------

#### Electric current

Rated current	160 A
Breaking and opening capacity Idm	0 kA

#### Equipment

With lock	Yes
Has mounting plate	No
Equipped with switch	No switch
Number of switches	0
Type of busbar chassis	Split chassis

#### Capacity

Number of modules	42
-------------------	----

#### Dimensions

Height	1600 mm
Width	600 mm
Depth	250 mm

#### Cover, door

Door/cover is transparent	No
---------------------------	----

#### Materials

Material	Stainless steel
Colour	Stainless steel

#### Safety

Protection class	Isolation class I
Impact resistance IK	IK05
Ingress Protection (IP) class	IP66
Locking type	3-point lever Key lock

#### Architecture

Number of poles	90
-----------------	----