



JPE0636S40TW1

**DB, elite, 400A, 6+36Pole, 400A ISO-WH.1200x600x250mm**

**Technical Features**

**Connection**

Number of accessible phases 42

**Installation, mounting**

Mounting on Surface mounting

**Electric current**

Rated current 375 A

Breaking and opening capacity I<sub>dm</sub> 0 kA

**Equipment**

With lock Yes

Has mounting plate No

Equipped with switch No switch

Number of switches 0

Type of busbar chassis Split chassis

**Capacity**

Number of modules 42

**Weight**

Weight 60 kg

**Dimensions**

Height 1200 mm

Width 600 mm

Depth 250 mm

**Cover, door**

Door/cover is transparent No

**Materials**

Material Steel

RAL code 7035

Colour Light grey

**Safety**

Protection class Isolation class I

Impact resistance IK IK05

Ingress Protection (IP) class IP66

Locking type 3-point lever  
Key lock

**Architecture**

Number of poles 42