Product Datasheet
JPE4818S16DS

JPE4818S16DS1

DB, elite, 48/18Pole, 160A ISO-DIN-SS, 1400x600x250mm

Technical Features

Connection	
Number of accessible phases	66
Installation, mounting	
Mounting on	Surface mounting
Electric current	
Rated current	160 A
Equipment	
With lock	Yes
Has mounting plate	No
Equipped with switch	Isolator
Number of switches	1
Type of busbar chassis	Split chassis
Capacity	
Number of modules	42
Weight	
Weight	64 kg
Dimensions	
Height	1400 mm
Width	600 mm
Depth	250 mm
Cover, door	
Door/cover is transparent	No
Materials	
Material	Stainless steel
Colour	Stainless steel
Safety	
Protection class	Isolation class I
Impact resistance IK	IK05
Ingress Protection (IP) class	IP66
Locking type	3-point lever Key lock
Architecture	
Number of poles	66
Sustainability	
RoHS conform	Yes