



JPD2400S25DW-M

DB, apex+, 24Pole, Meter, 250A Isolator 2x8 Mod+26 Mod, grey,1200x600x200mm

Technical Features

Installation, mounting

Mounting on Surface mounting

Electric current

Rated current 250 A
 Breaking and opening capacity I_{dm} 0 kA

Equipment

With lock Yes
 Has mounting plate No
 Equipped with switch No switch
 Number of switches 0
 Type of busbar chassis Fixed load chassis with CT integrated

Capacity

Number of modules 42

Weight

Weight 65 kg

Dimensions

Height 1200 mm
 Width 600 mm
 Depth 200 mm

Cover, door

Door/cover is transparent No

Materials

Material Steel
 RAL code 7035
 Colour Light grey

Safety

Protection class Isolation class I
 Impact resistance IK IK05
 Ingress Protection (IP) class IP43
 Locking type 3-point lever

Architecture

Number of poles 24