



JPD4842S25DW-M

DB, apex+, 48/42Pole, Meter,250A Isolator Twin, 8 Modules, grey, 1800x600x200mm

Technical Features

Connection

Number of accessible phases 90

Installation, mounting

Mounting on Surface mounting

Electric current

Rated current 250 A

Equipment

With lock Yes

Has mounting plate No

Equipped with switch Isolator

Number of switches 1

Type of busbar chassis Split chassis with CT integrated

Capacity

Number of modules 42

Weight

Weight 70 kg

Dimensions

Height 1800 mm

Width 600 mm

Depth 200 mm

Cover, door

Door/cover is transparent No

Materials

Material Steel

RAL code 7035

Colour Light grey

Safety

Protection class Isolation class I

Impact resistance IK IK05

Ingress Protection (IP) class IP43

Locking type 3-point lever
Key lock

Architecture

Number of poles 96

Sustainability

RoHS conform Yes