Product Datasheet
JPE6030S25DW-M



JPE6030S25DW-M

DB, elite, 60/30Pole, Meter, 250A Isolator Twin, 8 Modules, grey,1800x600x250mm

Technical Features

Connection	
Number of accessible phases	90
Installation, mounting	
Mounting on	Surface mounting
Electric current	
Rated current	250 A
Equipment	
With lock	Yes
Has mounting plate	No
Equipped with switch	Isolator
Number of switches	1
Type of busbar chassis	Split chassis with CT integrated
Capacity	
Number of modules	42
Weight	
Weight	79 kg
Dimensions	
Height	1800 mm
Width	600 mm
Depth	250 mm
Cover, door	
Door/cover is transparent	No
Materials	
Material	Steel
RAL code	7035
Colour	Light grey
Safety	
Protection class	Isolation class I
Impact resistance IK	IK05
Ingress Protection (IP) class	IP66
Locking type	3-point lever Key lock
Architecture	
Number of poles	90