



JPD6000S25DW-M

**DB, apex+, 60Pole, Meter, 250A Isolator 2x8 Mod+26 Mod, grey, 1400x600x200mm**

### Technical Features

#### Connection

Number of accessible phases	60
-----------------------------	----

#### Installation, mounting

Mounting on	Surface mounting
-------------	------------------

#### Electric current

Rated current	250 A
Breaking and opening capacity Idm	0 kA

#### Equipment

With lock	Yes
Has mounting plate	No
Equipped with switch	No switch
Number of switches	0
Type of busbar chassis	Fixed load chassis with CT integrated

#### Capacity

Number of modules	42
-------------------	----

#### Dimensions

Height	1400 mm
Width	600 mm
Depth	200 mm

#### Cover, door

Door/cover is transparent	No
---------------------------	----

#### Materials

Material	Steel
RAL code	7035
Colour	Light grey

#### Safety

Protection class	Isolation class I
Impact resistance IK	IK05
Ingress Protection (IP) class	IP43
Locking type	3-point lever

#### Architecture

Number of poles	60
-----------------	----