



JPD4800S25DW-M

DB, apex+, 48Pole, Meter, 250A Isolator 2x8 Mod+26 Mod,grey,1200x600x200mm

Technical Features

Connection

| | |
|-----------------------------|----|
| Number of accessible phases | 48 |
|-----------------------------|----|

Installation, mounting

| | |
|-------------|------------------|
| Mounting on | Surface mounting |
|-------------|------------------|

Electric current

| | |
|-----------------------------------|-------|
| Rated current | 250 A |
| Breaking and opening capacity Idm | 0 kA |

Equipment

| | |
|------------------------|---------------------------------------|
| With lock | Yes |
| Has mounting plate | No |
| Equipped with switch | No switch |
| Number of switches | 0 |
| Type of busbar chassis | Fixed load chassis with CT integrated |

Capacity

| | |
|-------------------|----|
| Number of modules | 42 |
|-------------------|----|

Dimensions

| | |
|--------|---------|
| Height | 1400 mm |
| Width | 600 mm |
| Depth | 200 mm |

Cover, door

| | |
|---------------------------|----|
| Door/cover is transparent | No |
|---------------------------|----|

Materials

| | |
|----------|------------|
| Material | Steel |
| RAL code | 7035 |
| Colour | Light grey |

Safety

| | |
|-------------------------------|-------------------|
| Protection class | Isolation class I |
| Impact resistance IK | IK05 |
| Ingress Protection (IP) class | IP43 |
| Locking type | 3-point lever |

Architecture

| | |
|-----------------|----|
| Number of poles | 48 |
|-----------------|----|