



JPD3012S25DW-M

DB, apex+, 30/12Pole, Meter, 250A Isolator Twin, 8 Modules, grey,1400x600x200mm

#### Technical Features

##### Connection

Number of accessible phases	42
-----------------------------	----

##### Installation, mounting

Mounting on	Surface mounting
-------------	------------------

##### Electric current

Rated current	250 A
Breaking and opening capacity Idm	0 kA

##### Equipment

With lock	Yes
Has mounting plate	No
Equipped with switch	No switch
Number of switches	0
Type of busbar chassis	Split chassis with CT integrated

##### Capacity

Number of modules	42
-------------------	----

##### Dimensions

Height	1400 mm
Width	600 mm
Depth	200 mm

##### Cover, door

Door/cover is transparent	No
---------------------------	----

##### Materials

Material	Steel
RAL code	7035
Colour	Light grey

##### Safety

Protection class	Isolation class I
Impact resistance IK	IK05
Ingress Protection (IP) class	IP43
Locking type	3-point lever Key lock

##### Architecture

Number of poles	42
-----------------	----