



JPE4224S25DW-M

DB, elite, 42/24Pole, Meter, 250A Isolator Twin, 8 Modules, grey,1600x600x250mm

Technical Features

Connection

Number of accessible phases 66

Installation, mounting

Mounting on Surface mounting

Electric current

Rated current 250 A

Breaking and opening capacity I_{dm} 0 kA

Equipment

With lock Yes

Has mounting plate No

Equipped with switch No switch

Number of switches 0

Type of busbar chassis Split chassis with CT integrated

Capacity

Number of modules 42

Weight

Weight 68 kg

Dimensions

Height 1600 mm

Width 600 mm

Depth 250 mm

Cover, door

Door/cover is transparent No

Materials

Material Steel

RAL code 7035

Colour Light grey

Safety

Protection class Isolation class I

Impact resistance IK IK05

Ingress Protection (IP) class IP66

Locking type 3-point lever
Key lock

Architecture

Number of poles 66

Sustainability

RoHS conform Yes