



JPD9600S25DW-M

**DB, apex+, 96Pole, Meter,250A Isolator 2x8 Mod+26 Mod, grey, 1600x600x200mm**

**Technical Features**

**Connection**

Number of accessible phases 96

**Installation, mounting**

Mounting on Surface mounting

**Electric current**

Rated current 250 A

Breaking and opening capacity I<sub>dm</sub> 0 kA

**Equipment**

With lock Yes

Has mounting plate No

Equipped with switch No switch

Number of switches 0

Type of busbar chassis Fixed load chassis with CT integrated

**Capacity**

Number of modules 42

**Weight**

Weight 70 kg

**Dimensions**

Height 1800 mm

Width 600 mm

Depth 200 mm

**Cover, door**

Door/cover is transparent No

**Materials**

Material Steel

RAL code 7035

Colour Light grey

**Safety**

Protection class Isolation class I

Impact resistance IK IK05

Ingress Protection (IP) class IP43

Locking type 3-point lever

**Architecture**

Number of poles 96