



JPD7218S25DW-M

**DB, apex+, 72/18Pole, Meter,250A Isolator Twin, 8 Modules, grey, 1800x600x200mm**

**Technical Features**

**Connection**

Number of accessible phases	90
-----------------------------	----

**Installation, mounting**

Mounting on	Surface mounting
-------------	------------------

**Electric current**

Rated current	250 A
---------------	-------

Breaking and opening capacity ldm	0 kA
-----------------------------------	------

**Equipment**

With lock	Yes
-----------	-----

Has mounting plate	No
--------------------	----

Equipped with switch	No switch
----------------------	-----------

Number of switches	0
--------------------	---

Type of busbar chassis	Split chassis with CT integrated
------------------------	----------------------------------

**Capacity**

Number of modules	42
-------------------	----

**Dimensions**

Height	1800 mm
--------	---------

Width	600 mm
-------	--------

Depth	200 mm
-------	--------

**Cover, door**

Door/cover is transparent	No
---------------------------	----

**Materials**

Material	Steel
----------	-------

RAL code	7035
----------	------

Colour	Light grey
--------	------------

**Safety**

Protection class	Isolation class I
------------------	-------------------

Impact resistance IK	IK05
----------------------	------

Ingress Protection (IP) class	IP43
-------------------------------	------

Locking type	3-point lever Key lock
--------------	---------------------------

**Architecture**

Number of poles	96
-----------------	----