



85421200

Universal Push button Dimmer Comfort 1gang (R,L, C, LED)

Technical Features

Voltage

Operating voltage	230 - 230 V
-------------------	-------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Material	Metal Plastic
----------	------------------

Dimensions

Built-in depth	32 mm
Height	71 mm
Width	71 mm
Depth	33.20 mm

Architecture

Control/operation element	Single push button
---------------------------	--------------------

Power

Power consumption standby	0.30 W
---------------------------	--------

Lighting

Dimmable 230 V LED lamp	3 - 250 W
LED lamp power	250 W

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Capacity

Number of modules	0
-------------------	---

Texts

Dimming principle	Automatic setting of load-dependent switching principle (autodetect process) Phase cut-on or cut-off according to load type, self-learning
Fuse	Short-circuit and overload-proof (electronic fuse)
Installation mode	With spreader claws
Type of connection	With screw terminals
Extension unit input	With extension unit input for push-button (NO contact), single-surface operation and motion detector extension unit
Operation and control	No Bluetooth interface

Equipment

Substation input	Yes
------------------	-----

Sustainability

RoHS conform	Yes
--------------	-----