



85122200



Switch insert 2gang, electronics

Technical Features

Voltage

Operating voltage 230 - 230 V

Controls and indicators

Applicable with movement sensor No

Frequency

Frequency 50 - 60 Hz

Lighting

Dimmable 230 V LED lamp 12 - 40 W

Use conditions

Operating temperature -5 - 45 °C

Dimensions

Built-in depth 32 mm

Texts

Dimming principle Automatic setting of load-dependent switching principle (autodetect process)

Extension unit input With 2 extension unit inputs for push-button (NO contact), single-surface operation

Fuse Short-circuit and overload-proof (electronic fuse)

Installation mode With spreader claws

Type of connection With screw terminals

Sustainability

RoHS conform Yes