



85122200



Switch insert 2gang, electronics

Technical Features

Voltage

Operating voltage	230 - 230 V
-------------------	-------------

Controls and indicators

Applicable with movement sensor	No
---------------------------------	----

Frequency

Frequency	50 - 60 Hz
-----------	------------

Lighting

Dimmable 230 V LED lamp	12 - 40 W
-------------------------	-----------

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Dimensions

Built-in depth	32 mm
----------------	-------

Texts

Dimming principle	Automatic setting of load-dependent switching principle (autodetect process)
Extension unit input	With 2 extension unit inputs for push-button (NO contact), single-surface operation
Fuse	Short-circuit and overload-proof (electronic fuse)
Installation mode	With spreader claws
Type of connection	With screw terminals

Sustainability

RoHS conform	Yes
--------------	-----