



3315397004



USB/3.5 mm audio soc. out., K.5, stainless steel matt, lacq.

Technical Features

Connection

| | |
|-----------------------|-----|
| Connector/plug type | USB |
| Number of connections | 2 |

Frequency

| | |
|-----------------|------------|
| Audio frequency | 20 - 20 Hz |
|-----------------|------------|

Materials

| | |
|----------------|-------------------------------------|
| Colour | Stainless steel |
| RAL code | 9022 |
| Surface finish | Matt |
| Material | Metal Plastic Stainless steel |
| Treatment | Varnished |

Dimensions

| | |
|------------------------------------|----------|
| Height | 71 mm |
| Width | 71 mm |
| Depth | 36.40 mm |
| Built-in depth flush-mounted boxes | 27 mm |
| Built-in depth | 24.90 mm |

Connectivity

| | |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

Equipment

| | |
|-----------------|-----|
| Shielded | Yes |
| With dust cover | No |

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Texts

| | |
|----------------------------------|-------------------------|
| Outlet | With straight outlet |
| Labelling | Without labelling field |
| Supporting plate/supporting ring | With supporting ring |