



3315392089



#### USB/3.5 mm audio soc. out., R.1/R.3, p. white glossy

##### Technical Features

###### Connection

Connector/plug type	USB
Number of connections	2

###### Frequency

Audio frequency	20 - 20 Hz
-----------------	------------

##### Materials

Colour	Polar white
RAL code	9010
Surface finish	Glossy
Material	Metal Plastic
Treatment	Untreated

##### Dimensions

Height	71 mm
Width	71 mm
Depth	36.40 mm
Built-in depth flush-mounted boxes	27 mm
Built-in depth	24.90 mm

##### Connectivity

Mounting type	Screw mounting
---------------	----------------

##### Equipment

Shielded	Yes
With dust cover	No

##### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

##### Texts

Outlet	With straight outlet
Labelling	Without labelling field
Supporting plate/supporting ring	With supporting ring

##### Suitable for

R.x	
-----	--

##### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes