




WMGSDP2B_OV

20A 1 Way Double Pole Switch Marked 'OVEN' Black

Technical Features

Electric current

Switching current	20 A
-------------------	------

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Voltage

Rated voltage	250 V
---------------	-------

Materials

Colour	Black
Surface finish	Glossy
Material	Urea formaldehyde
Treatment	Untreated

Identification

Assembly arrangement	Basic element with central cover plate
----------------------	--

Connectivity

Mounting type	Snap-on mounting
---------------	------------------

Controls and indicators

Number of buttons	1
-------------------	---

Dimensions

Dimensions	59 x 25 mm
Built-in depth	13.10 mm

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Architecture

Control/operation element	Single rocker
---------------------------	---------------

Electric current

Rated current	20 A
---------------	------

Texts

Lighting	Without lighting (cannot be illuminated)
Switch mode	2-pole

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes