



13293515

**Frame 2gang vertical for flush-mounted installation, with sealing W.1 light grey**

**Technical Features**

**Capacity**

Number of gangs	2
Number of modules	2

**Materials**

Colour	Grey
RAL code	7035
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated

**Dimensions**

Height	83 mm
Width	154 mm
Depth	38 mm

**Accessories**

Has labelling field	No
---------------------	----

**Installation, mounting**

Mounting-/Connection Position	Vertical
-------------------------------	----------

**Safety**

Ingress Protection (IP) class	IP20
Impact resistance IK	IK05

**Use conditions**

Operating temperature	-15 - 30 °C
-----------------------	-------------

**Texts**

Installation mode	With clamp/screw fastening With mounting adapter and sealing For flush-mounted and hollow wall mounting For vertical mounting
-------------------	--

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes