



TRM693G



**Module 1 flush mounted output 3A 230V + 2 inputs mains powered, KNX radio**

**Technical Features**

**Connectivity**

Radio protocol KNX Radio

**Settings**

Supported configuration mode ETS  
easy  
quicklink

**Connectivity**

Receiver category 2  
With bus system KNX No  
With bus system KNX radio Yes

**Dimensions**

Dimensions 40 x 40 mm  
Height 40 mm  
Width 40 mm  
Depth 20 mm  
Built-in depth 40 mm

**Electric current**

Rated current 3 A

**Materials**

Colour Light grey

**Equipment**

Radio frequency bidirectional Yes  
With switch for manual switch Yes

**Frequency**

Frequency 50 - 50 Hz  
Radio reception frequency 868.30 - 868.30 MHz

**Power**

Output power 690 W  
230 V incandescent and halogen lamp 500 W

**Voltage**

Operating voltage 230 - 230 V  
Rated operational voltage Ue 230 - 230 V  
System supply voltage 230 V AC

**Safety**

Ingress Protection (IP) class IP20

**Use conditions**

Operating temperature -10 - 50 °C

**Connection**

Cross-section rigid conductor 0.5 - 2.5 mm<sup>2</sup>  
Cross-section flexible conductor 0.5 - 1.5 mm<sup>2</sup>

**Texts**

Function Easy additional functions: +6 scenes  
Repeat function can be activated to increase the radio range  
Reset function (to factory setting)  
Installation mode For installation behind flush-mounted inserts  
Type of connection With screw-in lift terminals

---

**Sustainability**

---

RoHS conform

Yes