



TRM693G



Module 1 flush mounted output 3A 230V + 2 inputs mains powered, KNX radio

Technical Features

Connectivity

Radio protocol KNX Radio

Settings

Supported configuration mode ETS
easy
quicklink

Connectivity

Receiver category 2
 With bus system KNX No
 With bus system KNX radio Yes

Dimensions

Dimensions 40 x 40 mm
 Height 40 mm
 Width 40 mm
 Depth 20 mm
 Built-in depth 40 mm

Electric current

Rated current 3 A

Materials

Colour Light grey

Equipment

Radio frequency bidirectional Yes
 With switch for manual switch Yes

Frequency

Frequency 50 - 50 Hz
 Radio reception frequency 868.30 - 868.30 MHz

Power

Output power 690 W
 230 V incandescent and halogen lamp 500 W

Voltage

Operating voltage 230 - 230 V
 Rated operational voltage U_e 230 - 230 V
 System supply voltage 230 V AC

Safety

Ingress Protection (IP) class IP20

Use conditions

Operating temperature -10 - 50 °C

Connection

Cross-section rigid conductor 0.5 - 2.5 mm²
 Cross-section flexible conductor 0.5 - 1.5 mm²

Texts

Function Easy additional functions: +6 scenes
 Repeat function can be activated to increase the radio range
 Reset function (to factory setting)
 Installation mode For installation behind flush-mounted inserts
 Type of connection With screw-in lift terminals

Sustainability

RoHS conform

Yes