



TRM690G



Module 1 flush mounted output 200W, 2 wires + 2 inputs, KNX radio

Technical Features

Connectivity

Radio protocol	KNX Radio
----------------	-----------

Settings

Supported configuration mode	ETS easy quicklink
------------------------------	--------------------------

Connectivity

Receiver category	2
With bus system KNX	No
With bus system KNX radio	Yes

Dimensions

Dimensions	18 x 40 mm
Height	18 mm
Width	40 mm
Depth	18 mm
Built-in depth	40 mm

Electric current

Rated current	0.85 A
---------------	--------

Materials

Colour	Light grey
--------	------------

Equipment

Radio frequency bidirectional	Yes
With switch for manual switch	Yes

Frequency

Frequency	50 - 50 Hz
Radio reception frequency	868.30 - 868.30 MHz

Power

Output power	200 W
--------------	-------

Voltage

Operating voltage	230 - 230 V
Rated operational voltage U _e	230 - 230 V
System supply voltage	230 V AC

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Use conditions

Operating temperature	-15 - 45 °C
-----------------------	-------------

Connection

Cross-section rigid conductor	0.5 - 2.5 mm ²
Cross-section flexible conductor	0.5 - 1.5 mm ²

Texts

Function	Easy additional functions: +6 scenes Reset function (to factory setting)
Installation mode	For installation behind flush-mounted inserts
Type of connection	With screw-in lift terminals

Sustainability

RoHS conform	Yes
--------------	-----