



WMSSU83!HTR

13A FCU Switched Marked HEATER

Technical Features

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Voltage

Rated voltage	250 V
---------------	-------

Materials

Colour	White
Surface finish	Glossy
Material	Urea formaldehyde
Treatment	Untreated

Identification

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

Connectivity

Mounting type	Screw mounting
---------------	----------------

Controls and indicators

Number of buttons	1
-------------------	---

Dimensions

Dimensions	86 x 86 mm
Built-in depth	25.30 mm

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Electric current

Rated current	13 A
---------------	------

Texts

Installation mode	For flush-mounted and hollow wall mounting
Lighting	Without lighting (cannot be illuminated)
Switch mode	2-pole

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes