



WMPS11/FAN

10AX 1Gang 1 Way Wall Switch Marked 'FAN'

Technical Features

Electric current

Switching current 10 A

Installation, mounting

Mounting on Flush mounting

Voltage

Rated voltage 250 V

Materials

Colour White

Surface finish Glossy

Material Urea formaldehyde

Treatment Untreated

Identification

Assembly arrangement Basic element with full cover plate

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 1

Dimensions

Dimensions 86 x 86 mm

Built-in depth 12 mm

Safety

Ingress Protection (IP) class IP21

Architecture

Control/operation element Single rocker

Electric current

Rated current 10 A

Texts

Installation mode For flush-mounted and hollow wall mounting

Lighting Without lighting (cannot be illuminated)

Switch mode 1-way

Sustainability

REACH-SVHC free Yes

RoHS conform Yes