



6765792045

Soc.out. earth. pin, enhncd contact prot., screw-in lift term.,R.classic, bl.gl.

Technical Features

Voltage

Rated voltage 250 V

Electric current

Rated current 16 A

Frequency

Frequency 50 - 60 Hz

Materials

Colour Black

RAL code 9005

Surface finish Glossy

Material Thermoplastic

Treatment Untreated

Dimensions

Height 71 mm

Width 71 mm

Depth 40.90 mm

Number of units 1

Built-in depth 31.40 mm

Installation, mounting

Mounting on Flush mounting

Connectivity

Type of connection Screw terminal

Mounting type Screw mounting
Claw mounting

Equipment

Connector/plug type socket outlet Earthing pin

Rotated central insert Yes

With hinged lid No

With round protective earth pin Yes

With signal lamp No

With lock No

Accessories

Has labelling field No

Capacity

Number of modules 1

Safety

With enhanced contact protection Yes

Impact resistance IK IK05

Ingress Protection (IP) class IP20

Functions

With orientation lighting No

With function lighting No

Identification

With imprint No

Texts

| | |
|--------------------|------------------------------|
| Cover | Central cover plate |
| Protection | Enhanced contact protection |
| Type of connection | With screw-in lift terminals |

Suitable for

R.x / Serie R.classic

Sustainability

| | |
|--------------|-----|
| Halogen free | Yes |
| RoHS conform | Yes |