



6765792045

Soc.out. earth. pin, enhncd contact prot., screw-in lift term.,R.classic, bl.gl.

#### Technical Features

##### Electric current

Rated current	16 A
---------------	------

##### Voltage

Rated voltage	250 V
Nominal voltage	250 - 250 V

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Materials

Colour	Black
RAL code	9005
Surface finish	Glossy
Material	Thermoplastic
Treatment	Untreated

##### Dimensions

Height	71 mm
Width	71 mm
Depth	40.90 mm
Number of units	1
Built-in depth	31.40 mm

##### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

##### Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting Claw mounting

##### Equipment

Connector/plug type socket outlet	Earthing pin
Rotated central insert	Yes
With hinged lid	No
With round protective earth pin	Yes
With signal lamp	No
With lock	No

##### Accessories

Has labelling field	No
---------------------	----

##### Capacity

Number of modules	1
-------------------	---

##### Safety

With enhanced contact protection	Yes
Impact resistance IK	IK05
Ingress Protection (IP) class	IP20

##### Functions

With orientation lighting	No
With function lighting	No

##### Texts

Imprint	Without imprint
Cover	Central cover plate
Protection	Enhanced contact protection
Type of connection	With screw-in lift terminals

<b>Suitable for</b>	
R.x / Serie R.classic	
<b>Sustainability</b>	
RoHS conform	Yes