



6167032045

Soc. out. out earthing contact, R.1/R.3, black glossy

Technical Features

Electric current

| | |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

Voltage

| | |
|-----------------|-------------|
| Rated voltage | 250 V |
| Nominal voltage | 250 - 250 V |

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

Materials

| | |
|----------------|---------------|
| Colour | Black |
| RAL code | 9005 |
| Surface finish | Glossy |
| Material | Thermoplastic |
| Treatment | Untreated |

Dimensions

| | |
|------------------------------------|-------|
| Height | 71 mm |
| Width | 71 mm |
| Depth | 42 mm |
| Number of units | 1 |
| Built-in depth flush-mounted boxes | 31 mm |
| Built-in depth | 32 mm |

Connection

| | |
|---------------------|------------------|
| Connector/plug type | Plug-in terminal |
|---------------------|------------------|

Installation, mounting

| | |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

Connectivity

| | |
|--------------------|--------------------|
| Type of connection | Plug-in connection |
| With claw mounting | Yes |
| Mounting type | Screw mounting |

Equipment

| | |
|-----------------------------------|----------------------------|
| Connector/plug type socket outlet | Without protective contact |
| Rotated central insert | No |
| With hinged lid | No |
| With signal lamp | No |
| With lock | No |

Accessories

| | |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

Capacity

| | |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

Safety

| | |
|----------------------------------|------|
| With enhanced contact protection | No |
| Impact resistance IK | IK05 |
| Ingress Protection (IP) class | IP20 |

Functions

| | |
|---------------------------|----|
| With orientation lighting | No |
| With function lighting | No |

| | |
|--------------------|-------------------------------------|
| Texts | |
| Imprint | Without imprint |
| Cover | Central cover plate |
| Protection | Without enhanced contact protection |
| Type of connection | With plug-in terminals |

| | |
|---------------------|--|
| Suitable for | |
| R.x | |

| | |
|-----------------------|-----|
| Sustainability | |
| Halogen free | Yes |
| RoHS conform | Yes |