Product Datasheet
6167032089

6167032089

Soc. out. out earthing contact, R.1/R.3, p. white glossy

Technical Features

Voltage	
Rated voltage	250 V
Electric current	
Rated current	16 A
Frequency	
Frequency	50 - 60 Hz
Materials	
Colour	Polar white
RAL code	9010
Surface finish	Glossy
Material	Thermoplastic
Treatment	Untreated
Dimensions	
Height	71 mm
Width	71 mm
Depth	42 mm
Number of units	1
Built-in depth flush-mounted boxes	31 mm
Built-in depth	32 mm
Connection	
Connector/plug type	Plug-in terminal
Installation, mounting	
Mounting on	Flush mounting
Connectivity	
Type of connection	Plug-in connection
With claw mounting	Yes
Mounting type	Screw mounting
Equipment	
Connector/plug type socket outlet	Without protective contact
Rotated central insert	No
With hinged lid	No
With signal lamp	No
With lock	No
Accessories	
Has labelling field	No
Capacity	
Number of modules	1
Safety	
With enhanced contact protection	No
Impact resistance IK	IK05
Ingress Protection (IP) class	IP20
Functions	
With orientation lighting	No
With function lighting	No
Identification	
With imprint	No

Texts

Cover	Central cover plate
Protection	Without enhanced contact protection
Type of connection	With plug-in terminals

Suitable for

R.x

Sustainability

Halogen free	Yes
RoHS conform	Yes