



3315416084

VGA socket outlet with screw-in lift terminals, Q.x, alu velvety, lacquered

Technical Features

Connection

Connector/plug type	VGA
Number of connections	1

Frequency

Frequency video	160 MHz
-----------------	---------

Materials

Colour	Aluminium
RAL code	9006
Surface finish	Velvety
Material	Metal Plastic
Treatment	Varnished

Dimensions

Height	71 mm
Width	71 mm
Depth	23.50 mm
Built-in depth flush-mounted boxes	13 mm

Connectivity

Mounting type	Screw mounting
---------------	----------------

Equipment

Shielded	Yes
With dust cover	No

Safety

Ingress Protection (IP) class	IP20
Impact resistance IK	IK02

Texts

Outlet	With straight outlet
Labelling	Without labelling field
Supporting plate/supporting ring	With supporting ring

Suitable for

Q.x	
-----	--

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes