



3315417006



VGA soc. out., screw-in lift terminals, K.1, ant. matt, lacq.

**Technical Features**

**Connection**

Connector/plug type	VGA
Conductor cross-section	1.50 - 1.50 mm <sup>2</sup>
Number of connections	1

**Frequency**

Frequency video	160 MHz
-----------------	---------

**Materials**

Colour	Anthracite
RAL code	7021
Surface finish	Matt
Material	Metal Plastic
Treatment	Varnished

**Dimensions**

Height	71 mm
Width	71 mm
Depth	23.50 mm
Built-in depth flush-mounted boxes	13 mm

**Connectivity**

Mounting type	Screw mounting
---------------	----------------

**Equipment**

Shielded	Yes
With dust cover	No

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Texts**

Outlet	With straight outlet
Labelling	Without labelling field
Supporting plate/supporting ring	With supporting ring

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes