



3315417009



VGA soc. out., screw-in lift terminals, K.1, p. white glossy

Technical Features

Connection

|                         |                             |
|-------------------------|-----------------------------|
| Connector/plug type     | VGA                         |
| Conductor cross-section | 1.50 - 1.50 mm <sup>2</sup> |
| Number of connections   | 1                           |

Frequency

|                 |         |
|-----------------|---------|
| Frequency video | 160 MHz |
|-----------------|---------|

Materials

|                |                  |
|----------------|------------------|
| Colour         | Polar white      |
| RAL code       | 9010             |
| Surface finish | Glossy           |
| Material       | Metal<br>Plastic |
| Treatment      | Untreated        |

Dimensions

|                                    |          |
|------------------------------------|----------|
| Height                             | 71 mm    |
| Width                              | 71 mm    |
| Depth                              | 23.50 mm |
| Built-in depth flush-mounted boxes | 13 mm    |

Connectivity

|               |                |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

Equipment

|                 |     |
|-----------------|-----|
| Shielded        | Yes |
| With dust cover | No  |

Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Texts

|                                  |                         |
|----------------------------------|-------------------------|
| Outlet                           | With straight outlet    |
| Labelling                        | Without labelling field |
| Supporting plate/supporting ring | With supporting ring    |

Sustainability

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |