



3315406084

**VGA socket outlet, Q.x, aluminium velvety, lacquered**

**Technical Features**

**Connection**

Connector/plug type	VGA
Number of connections	1

**Frequency**

Frequency video	160 MHz
-----------------	---------

**Materials**

Colour	Aluminium
RAL code	9006
Surface finish	Velvety
Material	Metal Plastic
Treatment	Varnished

**Dimensions**

Height	71 mm
Width	71 mm
Depth	23.50 mm
Built-in depth flush-mounted boxes	14 mm
Built-in depth	12 mm

**Connectivity**

Mounting type	Screw mounting
---------------	----------------

**Equipment**

Shielded	Yes
With dust cover	No

**Safety**

Ingress Protection (IP) class	IP20
Impact resistance IK	IK02

**Texts**

Outlet	With straight outlet
Labelling	Without labelling field
Supporting plate/supporting ring	With supporting ring

**Suitable for**

Q.x	
-----	--

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes