



3315411404



VGA soc. out., screw-in lift terminals, B.7, al., matt, lacq.

Technical Features

Connection

Connector/plug type	VGA
Number of connections	1

Frequency

Frequency video	160 MHz
-----------------	---------

Materials

Colour	Aluminium
RAL code	9006
Surface finish	Matt
Material	Metal Plastic
Treatment	Varnished

Dimensions

Height	71 mm
Width	71 mm
Depth	23.50 mm
Built-in depth flush-mounted boxes	13 mm

Connectivity

Mounting type	Screw mounting
---------------	----------------

Equipment

Shielded	Yes
With dust cover	No

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Texts

Outlet	With straight outlet
Labelling	Without labelling field
Supporting plate/supporting ring	With supporting ring

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes