



GD313H

Enclosure,gamma,surface mounting,39 Modules, version Ireland

Technical Features

Installation, mounting

| | |
|-------------|------------------|
| Mounting on | Surface mounting |
|-------------|------------------|

Electric current

| | |
|---------------|------|
| Rated current | 63 A |
|---------------|------|

Equipment

| | |
|----------------------------|-----|
| Number of rails | 3 |
| Number of rows | 3 |
| Number of section in width | 1 |
| With lock | No |
| Has neutral terminal block | Yes |

Capacity

| | |
|-------------------|----|
| Number of modules | 39 |
|-------------------|----|

Dimensions

| | |
|--------|--------|
| Height | 500 mm |
| Width | 250 mm |
| Depth | 103 mm |

Cover, door

| | |
|-------------------------|---|
| Number of cabinet doors | 0 |
| Number of locks | 0 |

Dimensions

| | |
|-----------------------|----|
| Number of width units | 13 |
|-----------------------|----|

Cover, door

| | |
|---------------------------|----|
| Door/cover is transparent | No |
|---------------------------|----|

Materials

| | |
|----------|------------|
| Material | Plastic |
| RAL code | 9010 |
| Colour | Pure white |

Equipment

| | |
|-----------------------------|-----|
| Has earthing terminal block | Yes |
| Has mounting plate | No |

Safety

| | |
|-------------------------------|--------------|
| Impact resistance IK | IK05 |
| Ingress Protection (IP) class | IP30 |
| Locking type | Without lock |

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform | Yes |