



ECP300C

3 Phase kWhmeter via CT 1A or 5A 4M S0 MID

Technical Features

Architecture

Type of pole	3P+N
--------------	------

Electric current

Rated current	5 A
---------------	-----

Capacity

Number of modules	4
-------------------	---

Dimensions

Height	90 mm
Width	72 mm
Depth	60 mm

Equipment

Type of pulse generator	Electrical
-------------------------	------------

Compatibility

Suitable for	Purchase/supply
--------------	-----------------

Installation, mounting

Nominal tightening torque	1 - 1 Nm
Mounting on	DIN rail

Mechanical features

Nominal tightening torque digital terminal	0.50 - 0.50 Nm
--	----------------

Measurement

Measuring system	Measurement transformer
Type of measuring instrument	Electronic
Current measurement range	0.01 - 6.0 A
Measurement range voltage Ph-N	92 - 276 V
Measurement range voltage Ph-Ph	160 - 480 V
Frequency measuring range	45 - 65 Hz

Power supply

Number of phases for power supply	4
-----------------------------------	---

Functions

Accuracy class	B
Tariff type	T1...T2 (230 V AC)/-
Is calibrated	Yes

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Use conditions

Operating temperature	-25 - 55 °C
Storage/transport temperature	-25 - 70 °C

Power

Power consumption VA	2 VA
Total power loss under IN	0.60 W

Electric current

Maximum measuring circuit current	6 A
-----------------------------------	-----

Frequency

Frequency	50 - 50 Hz
-----------	------------

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes