



80161773



IP20



**Push-button 1gang, + RGB LED, internal temp. sensor, KNX - K.5, stainless steel**

**Technical Features**

**Installation, mounting**

Mounting on Flush mounting

**Use conditions**

Operating temperature -5 - 45 °C

**Electric current**

Bus current consumption data transfer 20 mA

**Functions**

With room temperature controller Yes

**Dimensions**

Height 55.10 mm

Width 70.90 mm

Depth 14.35 mm

**Equipment**

Number of actuation points 2

**Controls and indicators**

With LED indication Yes

**Materials**

Colour Stainless steel

RAL code 9022

Material Stainless steel  
Thermoplastic

Surface finish Matt

**Accessories**

Has labelling field Yes

**Screen**

With display No

**Texts**

Function Function for manual interruption of automatic functions already triggered

Protection With dismantling protection

Temperature Integrated temperature sensor with output of the measured values via object  
Integrated temperature sensor for operation as controller extension unit

**Sustainability**

REACH-SVHC free Yes

RoHS conform Yes