




80143321



KNX pb 3g fm, lab fields, RGB LED, intern temp KNX - Q.1/Q.3/Q.7, alu velv, lacq

Technical Features

Installation, mounting

Mounting on Flush mounting

Use conditions

Operating temperature -5 - 45 °C

Electric current

Bus current consumption data transfer 20 mA

Functions

With room temperature controller Yes

Dimensions

Height 58.70 mm

Width 58.70 mm

Depth 33.70 mm

Equipment

Number of actuation points 6

Controls and indicators

With LED indication Yes

Materials

Colour Aluminium

RAL code 9006

Material Thermoplastic

Surface finish Velvety

Accessories

Has labelling field Yes

Screen

With display No

Texts

Function Function for manual interruption of automatic functions already triggered

Protection With dismantling protection

Temperature Integrated temperature sensor with output of the measured values via object

Sustainability

REACH-SVHC free Yes

RoHS conform Yes